



TX-900MH impact printer

2.143.0200

Compact impact printer with USB and RS232 interface for

- 900 Touch Control (+)
- 915 KF Ti-Touch (+)
- 916 Ti-Touch (+)
- 917 Coulometer (+)
- 91X Meter (+)
- Eco Dosimat/Titrator (+)
- 877/848 Titrino plus (additional 6.2151.100 required)
- 865/876 Dosimat plus (additional 6.2151.100 required)
- 862 Compact Titrosampler (additional 6.2151.100 required)
- 870 KF Titrino plus (additional 6.2151.100 required)
- 899 Coulometer (additional 6.2151.100 required)

(+) Cable included in scope of delivery

Below, the accessories are grouped into Scope of delivery and Optional accessories.
Please keep this printout at hand for ordering replacement material.
These lists may be subject to change.

Scope of delivery 2.143.0200

Qt.	Order no.	Description	
1 PCS	1.143.0200	TX-900MH impact printer	
		Compact impact printer with USB and RS232 interface for 900 Touch Control 915 KF Ti-Touch 916 Ti-Touch 917 Coulometer 877/848 Titrino plus 865/876 Dosimat plus 91X meter (cable 6.2151.140) Eco Dosimat Eco Titrator Eco Coulometer 862 Compact Titrosampler 870 KF Titrino plus 899 Coulometer	
2 PCS	6.9001.070	Paper roll for TX-900MH	
		Paper roll for TX-900MH impact printer	
1 PCS	6.9002.070	Color ribbon for TX-900MH impact printer	

1 PCS

6.2151.140

Y cable USB A St - USB B St - Mini B St

Y cable for connection of a USB printer to the pH/Conductometers 912 / 913 / 914. This cable allows a printer and the power supply unit to be connected to the measuring instrument at the same time.



1 PCS

6.2134.040

RS-232 DB9 - IBM-PC(DB9) connecting cable

For the Metrohm RS-232 interface - PC connection. For Titrinos, Titrino plus and 756, 831 KF Coulometer, RS-232/USB Box



1 PCS

6.2151.020

Cable USB A - USB B 1.8 m

USB connecting cable



Optional accessories

Order no.	Description	
6.9002.070	Color ribbon for TX-900MH impact printer	
6.9001.070	Paper roll for TX-900MH Paper roll for TX-900MH impact printer	
6.2151.100	Adapter USB MINI (OTG) - USB A For connecting USB instruments.	
6.9001.080	Continuous adhesive labels for TX-900MH Self-adhesive paper roll for TX-900MH impact printer	