



833 Advanced IC Liquid Handling Suppressor Unit

2.833.0020

Chemical «packed bed anion suppressor. Patented MSM Metrohm Suppressor Module as stand-alone instrument or for retrofitting HPLC or IC systems. Solvent- and pressure-resistant. With two-channel pump for regeneration and rinsing solution.

Below, the accessories are grouped into Scope of delivery and Optional accessories.
Please keep this printout at hand for ordering replacement material.
These lists may be subject to change.


Scope of delivery 2.833.0020

Qt.	Order no.	Description
-----	-----------	-------------

1 PCS

1.753.0100

Suppressorblock kpl. **



1 PCS

6.1803.020

PTFE capillary 0.97 mm i.d. / 5 m

For all IC instruments



2 PCS

6.2128.180

Cable 762/830 - 752/753/754/833

Connecting IC Interface - IC Pump Unit, IC Suppressor Module, IC Dialysis Unit or IC Liquid Handling Unit



2 PCS

6.2744.010

Pressure screw 5x

With UNF 10/32 connection. For the connection of PEEK capillaries



1 PCS

6.2744.034

Coupling olive/UNF 10/32, 2x

Connection between pressure screw and pump tubing. 2 pieces. For IC instruments with peristaltic pump.




2 PCS

6.2744.160

Nozzle/UNF 10/32 coupling with security device

Security device for connecting pump tubing to a nozzle.



2 PCS



6.2821.120

Inline filter 2 µm

Inline filter 2 µm



Optional accessories

Order no.	Description	
6.1803.030	PTFE capillary 0.5 mm i.d. / 3 m Capillary for inline dialysis, for Dialysis Unit, IC Dialysis Sample Processor, IC Liquid Handling Dialysis Unit	
6.1826.060	Pump tubing (orange/yellow) For Compact IC , Personal IC , Basic IC	
6.2755.000	Tubing cartridge For the peristaltic pumps of IC instruments. Contact pressure adjustable.	
6.2821.130	Spare filter for inline filter Spare filter for inline filter.	

6.2832.000

MSM Rotor A

Suppressor rotor for all IC instruments with MSM (Metrohm Suppressor Module)



6.2832.010

Connecting piece for MSM and MSM-LC

With inlets and outlets. For all IC instruments with MSM (Metrohm Suppressor Module).

For replacement in Professional IC instruments of generations 850, 881, 882, and 883 (manufactured before 2017).

