



943 Professional Thermostat Vario

2.943.0210

The 943 Professional Thermostat Vario is a stand-alone column oven for up to two columns with a maximum length of 150 mm. It captivates by its fast heating rate and the possibility of operating two separation columns together at up to 80°C.

Below, the accessories are grouped into Scope of delivery and Optional accessories.

Please keep this printout at hand for ordering replacement material.

These lists may be subject to change.

Scope of delivery 2.943.0210

Qt.	Order no.	Description
1 PCS	1.943.0010	943 Professional Thermostat / Reactor Vario



1 PCS

6.1831.100

PEEK capillary 0.25 mm i.d., 1 m



1 PCS

6.2151.020

Cable USB A - USB B 1.8 m

USB connecting cable



1 PCS

6.2621.100

3 mm hex key for IC Sample Processors



1 PCS

6.2621.140

Hexagon key 2.5 mm



1 PCS

6.2744.040

2 x UNF 10/32 coupling

For connecting 1/16 in. capillaries. For IC instruments



1 PCS

6.2744.070

Pressure screw short

Short version. With UNF 10/32 connection. 5 pieces. For the connection of PEEK capillaries




1 PCS

6.2845.600

Column holder complete to Professional Thermostat

Intelligent column holder for the Professional Thermostat




Optional accessories

Order no.	Description	
6.1015.100	Metrosep BP 1 Guard/2.0	The Metrosep BP 1 Guard/2.0 is used to generate a sufficiently high working pressure in the flow path of post-column reagents. They are used in combination with a high-pressure pump for conveying the post-column reagent in the Professional Reactor. 
6.1602.200	Bottle cap 2 x M6, 1 x M8 to 6.1608.120	Bottle cap for eluent bottles made of PP for eluents, post-column derivatization solutions, etc. The PP eluent bottle can withstand gas pressure when this bottle cap is used. 
6.1608.120	PP eluent bottle, 2 L	Eluent bottle for applications where glass should be avoided. 
6.2061.100	Bottle holder for Professional IC instruments	Instrument cover and bottle holder for Professional IC instruments. 



Connects an IC module with the footprint of a Professional IC with a Compact IC




Intelligent reactor plate with reactor for PCR applications.



6.2845.110

HT reactor plate, complete, for Professional Reactor


Reactor plate with reactor for PCR applications at high temperatures (> 120 °C). With PEEK reactor capillaries.



6.2845.200

Reactor complete to 6.2845.100

Spare reactor for the reactor plate



6.2845.210

HT reactor, complete, for 6.2845.110

Reactor for PCR applications at high temperatures (> 120 °C). With PEEK reactor capillaries.

