




944 Professional UV/VIS Detector Vario

2.944.0010

The 944 Professional UV/VIS Detector Vario is the intelligent UV/VIS detector from Metrohm. It permits a secure and reliable quantification of substances active in the ultraviolet or visible range. Detection takes place via a Diode Array.

Below, the accessories are grouped into Scope of delivery and Optional accessories. Please keep this printout at hand for ordering replacement material. These lists may be subject to change.

Scope of delivery 2.944.0010

Qt.	Order no.	Description
1 PCS	1.944.0010	944 Professional UV/VIS Detector Vario

The 944 Professional UV/VIS Detector Vario is the intelligent UV/VIS detector from Metrohm. It permits a secure and reliable quantification of substances active in the ultraviolet or visible range. Detection takes place via a Diode Array.



2 PCS

6.1831.100

PEEK capillary 0.25 mm i.d., 1 m



1 PCS

6.2151.020

Cable USB A - USB B 1.8 m

USB connecting cable



1 PCS

6.2744.070

Pressure screw short

Short version. With UNF 10/32 connection. 5 pieces. For the connection of PEEK capillaries



1 PCS

6.2839.130

Flow-through cell for 944

PEEK flow-through cell for 944 Professional UV/VIS Detector Vario



Optional accessories

Order no.	Description	
6.2061.100	Bottle holder for Professional IC instruments Instrument cover and bottle holder for Professional IC instruments.	
6.2061.110	Tray with sensor for Professional IC Instruments	
6.2061.120	System Connector Connects an IC module with the footprint of a Professional IC with a Compact IC	
2.943.0110	943 Professional Reactor Vario The 943 Professional Reactor Vario is a heatable reactor, especially developed for pre- and post-column derivatization. It captivates by its robustness, the fast heating rate and the possibility of carrying out reactions at up to 150 °C.	

2.943.0210

943 Professional Thermostat Vario


The 943 Professional Thermostat Vario is a stand-alone column oven for up to two columns with a maximum length of 150 mm. It captivates by its fast heating rate and the possibility of operating two separation columns together at up to 80°C.



6.2764.000

Replacement seals to 62839130

Set of seals for Flow cell 10 mm (6.2839.130) to UV/VIS instruments



6.2804.060

Deuterium lamp (UV) for UV/VIS instruments

Replacement bulb for the UV range



6.2804.100

Halogen lamp (Vis) for Professional UV/VIS Detector

Spare lamp for the visible range for the 944 Professional UV/VIS Detector Vario

