




# 945 Professional Detector Vario – Conductivity

2.945.0010

Intelligent stand-alone detector equipped with a high-performance IC Conductivity Detector. For use with intelligent IC instruments or as independent conductivity detector.

Below, the accessories are grouped into Scope of delivery and Optional accessories.

Please keep this printout at hand for ordering replacement material.

These lists may be subject to change.

## Scope of delivery 2.945.0010

| Qt.   | Order no.  | Description                                    |
|-------|------------|------------------------------------------------|
| 1 PCS | 1.945.0010 | 945 Professional Detector Vario – Conductivity |

Intelligent stand-alone detector equipped with a high-performance IC Conductivity Detector. For use with intelligent IC instruments or as independent conductivity detector.



1 PCS

6.1831.030

PEEK capillary 0.75 mm i.d. / 3 m

For all IC components.



---

1 PCS

6.2151.020

Cable USB A - USB B 1.8 m

USB connecting cable



---

1 PCS

6.2744.014

Pressure screw 2x

With UNF 10/32 connection. For the connection of PEEK capillaries

