




947 Professional UV/VIS Detector Vario MW


2.947.0020

As an intelligent, multi-wavelength detector, the 947 Professional UV/VIS Detector Vario MW permits a secure and reliable quantification of substances active in the ultraviolet or visible range. Up to eight wavelengths can be freely selected. A diode array is used for detection.

Below, the accessories are grouped into Scope of delivery and Optional accessories. Please keep this printout at hand for ordering replacement material. These lists may be subject to change.

Scope of delivery 2.947.0020

Qt.	Order no.	Description
1 PCS	1.947.0020	Professional UV/VIS Detector Vario MW



2 PCS

6.1831.100

PEEK capillary 0.25 mm i.d., 1 m



1 PCS

6.2151.020

Cable USB A - USB B 1.8 m

USB connecting cable



1 PCS

6.2744.070

Pressure screw short

Short version. With UNF 10/32 connection. 5 pieces. For the connection of PEEK capillaries



1 PCS

6.2839.130

Flow-through cell for 944

PEEK flow-through cell for 944 Professional UV/VIS Detector Vario



Optional accessories

Order no.	Description	
6.2804.110	Deuterium lamp (UV) for 947 Professional UV/VIS Detector Vario SW/MW Replacement deuterium lamp for 947 Professional UV/VIS Detector Vario SW/MW.	
6.2630.100	Cover for the deuterium lamp shaft on the UV/VIS Detector SW/MW	
6.2630.200	Cover for the VIS lamp shaft on the UV/VIS Detector SW/MW	
2.943.0110	943 Professional Reactor Vario The 943 Professional Reactor Vario is a heatable reactor, especially developed for pre- and post-column derivatization. It captivates by its robustness, the fast heating rate and the possibility of carrying out reactions at up to 150 °C.	

The 943 Professional Thermostat Vario is a stand-alone column oven for up to two columns with a maximum length of 150 mm. It captivates by its fast heating rate and the possibility of operating two separation columns together at up to 80°C.



Instrument cover and bottle holder for Professional IC instruments.




Connects an IC module with the footprint of a Professional IC with a Compact IC



6.2764.000

Replacement seals to 62839130

Set of seals for Flow cell 10 mm (6.2839.130) to UV/VIS instruments



6.2804.120

Halogen lamp II (VIS) for 947 Professional UV/VIS Detector

Spare lamp for the visible range for the 947 Professional UV/VIS Detector
Only works in conjunction with 62630010 holder for halogen lamp II

