



High Throughput Lab-grade Raman Probe (785 nm), 5m

607510150

High-throughput lab-grade fiber optic Raman probe assembly with trigger button. 5 meter fiber length.

Compatible with i-Raman NxG 785S and 785H models.

Below, the accessories are grouped into Scope of delivery and Optional accessories.

Please keep this printout at hand for ordering replacement material.

These lists may be subject to change.

Scope of delivery 607510150


Qt.	Order no.	Description
-----	-----------	-------------

1 PCS

607510430

Distance Regulator Cap

Distance regulator cap for standard lab-grade Raman probe shaft.



1 PCS

607510220

Standard Shaft for Lab-Grade Probe (785 nm)

Replacement shaft for 785 nm excitation lab-grade Raman probe assembly. Working distance 5.5 mm.

