



Connecting cable, leak sensor

6.2141.430

Connecting cable between connection box and leak sensor inlet of the IC

Below, the accessories are grouped into Scope of delivery and Optional accessories.

Please keep this printout at hand for ordering replacement material.

These lists may be subject to change.

Optional accessories

Order no.	Description
6.2141.410	Remote cable, IC - Agilent ICP-MS Connecting cable for synchronization of Metrohm IC Systems (930 IC Flex and 940 Professional IC) and Agilent ICP-MS systems



6.2149.310 Connection Box, remote control, ICP-MS

Connector for use as interface between Metrohm IC (Remote Box MSB) and Agilent ICP-MS in MassHunter 5.3 and higher.



6.2141.420 Connecting cable, Remote Box MSB

Connecting cable between connection box and Remote Box MSB

