



Macro pump head PEEK

6.2824.130

Macro pump head for intelligente IC instruments, flow range 0.1...20 mL/min, maximum pressure 12.5 MPa.

Below, the accessories are grouped into Scope of delivery and Optional accessories.

Please keep this printout at hand for ordering replacement material.

These lists may be subject to change.

Scope of delivery 6.2824.130

Qt.	Order no.	Description
2 PCS	6.2741.040	PE/PTFE piston seal, macro
		For all macro pump heads



1 PCS

6.2824.170

Inlet valve PEEK

Metal-free check valve for the inlet side of the IC pump heads of the devices 940, 930, 925, 883, 882, 881, and 850.



1 PCS

6.2824.160

Outlet valve PEEK

Metal-free check valve for the outlet side of the IC pump heads of the devices 940, 930, 925, 883, 882, 881, and 850.

