



Aspiration tubing with coupling, for IC

6.5332.010

Below, the accessories are grouped into Scope of delivery and Optional accessories.
Please keep this printout at hand for ordering replacement material.
These lists may be subject to change.

Scope of delivery 6.5332.010

Qt.	Order no.	Description
1 PCS	6.1834.080	Aspiration tubing, 2 m
Eluent aspiration tubing for Professional IC devices for connection to the IC degasser. Optional: 6.2744.210 tubing adapter for aspiration filter 6.2821.090 aspiration filter 6.2744.230 adapter 1/16 in/2.5 mm for connecting the aspiration tubing to the IC pump if no degasser is present		



1 PCS

6.2621.050

1/4 in. wrench

For 1/4 in. screws. For IC instruments



1 PCS

6.2739.000

Wrench

For tightening connectors




1 PCS

6.2744.210

Tubing adapter for aspiration filter (ProfilC)

For Professional IC instruments



1 PCS

6.2744.230

1/16 in. / 2.5 mm adapter

Adapter for the connection of the aspiration tubing to the IC pump.
Contains the pressure screw for the PEEK capillary.

