



IC equipment Wall-Jet cell: without electrodes

6.5337.000

Equipment comprised of Wall-Jet cell with additional accessories, without electrode.

Below, the accessories are grouped into Scope of delivery and Optional accessories.

Please keep this printout at hand for ordering replacement material.

These lists may be subject to change.

Scope of delivery 6.5337.000

Qt.	Order no.	Description
1 PCS	6.1257.810	50 µm spacer for the Wall-Jet cell.
		50 µm spacer for the amperometric Wall-Jet cell, 3 pcs.



1 PCS

6.1257.830

25 µm spacer for the Wall-Jet cell

25 µm spacer for the amperometric Wall-Jet cell, 3 pcs.



1 PCS

6.1831.010

PEEK capillary 0.25 mm i.d. / 3 m

For all IC components.



1 PCS

6.2621.140

Hexagon key 2.5 mm



1 PCS

6.2744.014

Pressure screw 2x

With UNF 10/32 connection. For the connection of PEEK capillaries



1 PCS

6.2802.000

Polishing set for solid-state electrodes

Polishing set with 1 polishing cloth and about 2 g aluminum oxide powder (grain size 0.3 µm)

