




Continuous IC Package PP

2.930.8040

納品範囲 2.930.8040

Qt.	Order no.	説明
1 PCS	1.858.0020	858 Professional Sample Processor – Pump

858 プロフェッショナルサンプルプロセッサ - ポンプは、500 μ Lから500 mLまでのサンプルを処理します。サンプルは内蔵式双方向性の2チャンネルのペリスタリックポンプまたは800 ドジーノ電動ビュレットによって転送されます。



1 PCS

1.930.2560

930 Compact IC Flex Oven/SeS/PP/Deg

930 コンパクト IC Flex Oven/SeS/PP/Deg はカラムオープン、連続サプレッション、サプレッサー再生のためのペリスタリックポンプ、内蔵式脱気装置を備えたインテリジェントコンパクトIC装置です。この装置は任意の分離メソッドおよび検出メソッドによって使用することができます。

典型的な使用領域:

- 連続サプレッションおよび電気伝導度検出器による陰イオンの測定



1 PCS

6.02850.000

高圧デガッサー

高圧デガッサーは、溶離液生成時に発生する水素ガスの除去を行います。



1 PCS

6.02850.100

連続陰イオントラップ

連続陰イオントラップ (CT-A) は、溶離液から陰イオン性不純物と炭酸塩を除去します。



1 PCS


6.02850.200

溶離液生成カートリッジ A

溶離液生成カートリッジ A (EPC A) は、水の電気分解により、4 mol/L の水酸化物濃縮物から高純度の水酸化溶離液を生成します。陽イオン交換膜は、陽イオンの溶離液への選択的マイグレーションを可能にします。EPC A には、浄水装置と接続させて全自動で稼働可能な超純水が供給されます。



1 PCS 6.05000.300 付属品キット: CEP



3 PCS 6.1608.080 Bottle / 300 mL



1 PCS 6.1803.030 PTFE capillary 0.5 mm i.d. / 3 m




2 PCS 6.1826.360 Pump tubing LFL (white/white), 3 stoppers



1 PCS

6.1826.420

PharMed® pump tubing (orange/yellow), 3-
stopper



1 PCS

6.1831.060

PEEK capillary 0.5 mm i.d., 1 m



1 PCS

6.1831.160

PEEK capillary, 0.5 mm ID / 70 cm



1 PCS

6.2041.760

Sample rack 54 x 11 mL + 1 x 300 mL



1 PCS

6.2064.000

Beaker retainer for Advanced IC Sample Processor



1 PCS

6.2151.000

Cable USB A – mini-DIN 8-pin



1 PCS

6.2151.020

Cable USB A - USB B 1.8 m



1 PCS

6.2164.010

卓上電源アダプタ 100 - 240 V/24 V DC

卓上電源アダプタ 915 KF Ti-Touch、916 Ti-Touch、917 Coulometer
および全てのEco Titratoren / Eco Dosimat向け。



1 PCS

6.2621.300

Tool set for Advanced IC Sample Processors



1 PCS

6.2739.000

Wrench



1 PCS

6.2744.010

Pressure screw 5x



1 PCS

6.2744.014

Pressure screw 2x



2 PCS

6.2744.034

カップリング チューブニップル/UNF 10/32、2個

圧力調整ネジとポンプチューブを接続。2個。ペリスタリックポンプ付きIC装置用。



1 PCS

6.2744.070


Pressure screw short



2 PCS

6.2744.160

Nozzle/UNF 10/32 coupling with security device



1 PCS

6.2744.180


Pump tubing connector with security lock and filter



1 PCS

6.2751.110

Safety shield



1 PCS

6.2842.100

MSM-HC Rotor A、水酸化物



1 PCS

6.2846.010

Sample needle made of zirconium oxide with PEEK tip



1 PCS

6.5000.000

Accessory kit: Vario/Flex Basic



1 PCS

6.5000.010

Accessory kit: Vario/Flex ONE



1 PCS

6.5000.020

Accessory kit: Vario/Flex SeS



1 PCS

6.6059.421

MagIC Net 4.2 Compact: 1ライセンス

