



943 Professional Thermostat Vario

2.943.0210

943 プロフェッショナル Thermostat Varioは、最長150 mmまでの2つ以下のカラムのためのスタンドアローンカラムオープンです。この製品は、高速度加熱、80℃までの温度下において2つの分離カラムを一緒に稼働できることを特長としています。

納品範囲 2.943.0210

Qt.	Order no.	説明
1 PCS	1.943.0010	943 Professional Thermostat / Reactor Vario



1 PCS

6.1831.100

PEEK capillary 0.25 mm i.d., 1 m



1 PCS

6.2151.020

Cable USB A - USB B 1.8 m



1 PCS

6.2621.100

3 mm hex key for IC Sample Processors



1 PCS

6.2621.140

Hexagon key 2.5 mm



1 PCS

6.2744.040

2 x UNF 10/32 coupling



1 PCS

6.2744.070


Pressure screw short



1 PCS

6.2845.600

Column holder complete to Professional
Thermostat



オプションアクセサリ

Order no.	説明
6.1015.100	Metrosep BP 1 Guard/2.0 Metrosep BP 1 Guard/2.0は、ポストカラム試薬の流路に十分な高い作業圧力を生成するのに使用されます。これは搬送用高圧ポンプと組み合わせることで、専門リアクターでのポストカラム試薬の供給に使用されます。 
6.1602.200	Bottle cap 2 x M6, 1 x M8 to 6.1608.120 
6.1608.120	PP eluent bottle, 2 L 
6.2061.100	ボトルホルダー Professional IC 装置 Professional IC 装置のための装置カバーおよびボトルホルダー。 


6.2061.110 Tray with sensor for Professional IC Instruments



6.2061.120 System Connector



6.2744.330 Y connector 3 x UNF 10/32




6.2845.100 Reactor plate complete to Professional Reactor



6.2845.110 HT reactor plate, complete, for Professional Reactor



6.2845.200 Reactor complete to 6.2845.100



6.2845.210 HT reactor, complete, for 6.2845.110

