


## Zubehör-Kit: OMNIS IC L Module

6.05000.040

**納品範囲 6.05000.040**

| Order Number | 説明                                  | 数量    |
|--------------|-------------------------------------|-------|
| 6.01805.500  | FEP-Schlauch 1/8" RO - DEG, 1200 mm | 2 PCS |




|             |                              |       |
|-------------|------------------------------|-------|
| 6.01806.000 | PEEK製キャピラリー 0.18 mm 内径 / 2 m | 1 PCS |
|-------------|------------------------------|-------|



例えば2 mm 仕様のMetrosep Carb 2 カラム (6.01090.2 x0) 用の予熱キャピラリーとしてなど、高圧流路での使用向け。


|             |                                       |       |
|-------------|---------------------------------------|-------|
| 6.01831.100 | PEEK-Kapillare DEG - HPP, 240/0.75 mm | 2 PCS |
|-------------|---------------------------------------|-------|



6.01831.110

**PEEK-Kapillare HPP - INJ, 160/0.5 mm**


2 PCS



6.01831.140

**PEEK-Kapillare INJ - COL, 180/0.18 mm**


1 PCS



6.01831.180

**PEEK-Kapillare, INJ-COL, 280/0.18 mm**


1 PCS



6.02744.010

**flanschlose Verschraubung M6, 1/8", 2 Stk.**


2 PCS



6.02837.040

**Filterrohr**


2 PCS



6.05801.310

**Ablaufkit, L**


1 PCS



6.1825.210

**PEEK sample loop 20 µL**

2 PCS



6.2744.070

**Pressure screw short**

2 PCS



6.2744.320

PEEK coupling M6 / UNF 10/32

2 PCS

