



TX-900MH impact printer

2.143.0200

Compact impact printer with USB and RS232 interface for

- 900 Touch Control (+)
- 915 KF Ti-Touch (+)
- 916 Ti-Touch (+)
- 917 Coulometer (+)
- 91X Meter (+)
- Eco Dosimat/Titrator (+)
- 877/848 Titrino plus (additional 6.2151.100 required)
- 865/876 Dosimat plus (additional 6.2151.100 required)
- 862 Compact Titrosampler (additional 6.2151.100 required)
- 870 KF Titrino plus (additional 6.2151.100 required)
- 899 Coulometer (additional 6.2151.100 required)

(+) Cable included in scope of delivery

Phạm vi giao hàng 2.143.0200

Qt.	Order no.	Description
-----	-----------	-------------

1 PCS 1.143.0200 TX-900MH impact printer

Compact impact printer with USB and RS232 interface for

- 900 Touch Control
- 915 KF Ti-Touch
- 916 Ti-Touch
- 917 Coulometer
- 877/848 Titrino plus
- 865/876 Dosimat plus
- 91X meter (cable 6.2151.140)
- Eco Dosimat
- Eco Titrator
- Eco Coulometer
- 862 Compact Titrosampler
- 870 KF Titrino plus
- 899 Coulometer



2 PCS 6.9001.070 Paper roll for TX-900MH

Paper roll for TX-900MH impact printer



1 PCS 6.9002.070 Color ribbon for TX-900MH impact printer



1 PCS

6.2151.140

Y cable USB A St - USB B St - Mini B St

Y cable for connection of a USB printer to the pH/Conductometers 912 / 913 / 914. This cable allows a printer and the power supply unit to be connected to the measuring instrument at the same time.



1 PCS

6.2134.040

RS-232 DB9 - IBM-PC(DB9) connecting cable

For the Metrohm RS-232 interface - PC connection. For Titrinos, Titrino plus and 756, 831 KF Coulometer, RS-232/USB Box



1 PCS

6.2151.020

Cable USB A - USB B 1.8 m

USB connecting cable



Phụ kiện tùy chọn

Order no.	Description	
6.9002.070	Color ribbon for TX-900MH impact printer	
6.9001.070	Paper roll for TX-900MH Paper roll for TX-900MH impact printer	
6.2151.100	Adapter USB MINI (OTG) - USB A For connecting USB instruments.	
6.9001.080	Continuous adhesive labels for TX-900MH Self-adhesive paper roll for TX-900MH impact printer	