



819 Advanced IC Detector (PEEK)

2.819.0110

Top-class conductivity detector for measurements with and without chemical suppression. Temperature-stability better than 0.01 °C. Shielded by Faraday cage. Wet part and electronics clearly separated. Electronic suppression. PEEK version.

Phạm vi giao hàng 2.819.0110

Qt.	Order no.	Description
1 PCS	6.2125.090	RS-232 cable 1 m, 25-pin D – sub 25 RS-232 extension cable (1:1). Specially shielded.



1 PCS

6.2125.110

RS-232 cable 3 m, 25-pin – 9-pin

Connecting Metrohm RS-232 interface to PC. Used with pH Meters, Titrinos, KF Coulometers, VA Trace Analyzer.



1 PCS

6.2248.000

Magnetic shield for instrument identification

For IC Instruments



Phụ kiện tùy chọn

Order no.	Description
6.2134.140	Cable 771 (analog) - 819 Connection of analog and start signals to 771


