





947 Professional UV/VIS Detector Vario MW

2.947.0020

As an intelligent, multi-wavelength detector, the 947 Professional UV/VIS Detector Vario MW permits a secure and reliable quantification of substances active in the ultraviolet or visible range. Up to eight wavelengths can be freely selected. A diode array is used for detection.

Phạm vi giao hàng 2.947.0020

Qt.	Order no.	Description
1 PCS	1.947.0020	Professional UV/VIS Detector Vario MW



2 PCS

6.1831.100

PEEK capillary 0.25 mm i.d., 1 m



1 PCS

6.2151.020

Cable USB A - USB B 1.8 m

USB connecting cable



1 PCS

6.2744.070

Pressure screw short

Short version. With UNF 10/32 connection. 5 pieces. For the connection of PEEK capillaries



1 PCS

6.2839.130

Flow-through cell for 944

PEEK flow-through cell for 944 Professional UV/VIS Detector Vario



Phụ kiện tùy chọn

Order no.	Description	
6.2804.110	Deuterium lamp (UV) for 947 Professional UV/VIS Detector Vario SW/MW Replacement deuterium lamp for 947 Professional UV/VIS Detector Vario SW/MW.	
6.2630.100	Cover for the deuterium lamp shaft on the UV/VIS Detector SW/MW	
6.2630.200	Cover for the VIS lamp shaft on the UV/VIS Detector SW/MW	
2.943.0110	943 Professional Reactor Vario The 943 Professional Reactor Vario is a heatable reactor, especially developed for pre- and post-column derivatization. It captivates by its robustness, the fast heating rate and the possibility of carrying out reactions at up to 150 °C.	

The 943 Professional Thermostat Vario is a stand-alone column oven for up to two columns with a maximum length of 150 mm. It captivates by its fast heating rate and the possibility of operating two separation columns together at up to 80°C.



Instrument cover and bottle holder for Professional IC instruments.




Connects an IC module with the footprint of a Professional IC with a Compact IC



6.2764.000

Replacement seals to 62839130

Set of seals for Flow cell 10 mm (6.2839.130) to UV/VIS instruments



6.2804.120

Halogen lamp II (VIS) for 947 Professional UV/VIS Detector

Spare lamp for the visible range for the 947 Professional UV/VIS Detector
Only works in conjunction with 62630010 holder for halogen lamp II

