



# High Throughput Lab-grade Raman Probe (785 nm), 5m

607510150


High-throughput lab-grade fiber optic Raman probe assembly with trigger button. 5 meter fiber length.

Compatible with i-Raman NxG 785S and 785H models.

## Phạm vi giao hàng 607510150

| Qt.   | Order no. | Description            |
|-------|-----------|------------------------|
| 1 PCS | 607510430 | Distance Regulator Cap |

Distance regulator cap for standard lab-grade Raman probe shaft.



Replacement shaft for 785 nm excitation lab-grade Raman probe assembly. Working distance 5.5 mm.

