



Metrosep C 6 - 150/4.0

6.1051.420

The high-capacity C 6 material makes the Metrosep C 6 - 150/4.0 separation column the optimum solution for separating standard cations with high differences in concentration in conjunction with reasonable retention times. Drinking water with low ammonium contents can be determined with this column.

Phạm vi giao hàng 6.1051.420

Qt.	Order no.	Description
2 PCS	6.2744.060	Threaded stopper

For UNF 10/32. Stopper for IC, e.g. for the sealing of columns.



Phụ kiện tùy chọn

Order no.	Description	
6.1051.500	Metrosep C 6 Guard/4.0	
	The Metrosep C 6 Guard/4.0 contains the C 6 column material and is used to protect against particles and contamination. This considerably lengthens the service life of the analytical separation column. The Metrosep C 6 Guard/4.0 works according to the "On Column Guard System" and is screwed directly onto the respective separation column with virtually no dead volume.	
6.1051.510	Metrosep C 6 S-Guard/4.0	
	The Metrosep C 6 S-Guard/4.0 contains the C 6 column material and is used to protect it against particles and contamination. This considerably lengthens the service life of the analytical separation column.	