




Optrode

6.1115.000

Optical sensor for photometric titrations offering 8 different wavelengths. The wavelength can be switched using the software (tiamo 2.5 or higher) or with a magnet. The glass shaft is completely solvent-resistant and easy to clean. For example, this space-saving sensor is suitable for:

- Non-aqueous titrations in accordance with USP or EP
- Determinations of carboxyl end groups
- TAN/TBN in accordance with ASTM D974
- Sulfate determination
- Fe, Al, Ca in cement
- Water hardness
- Chondroitin sulfate in accordance with USP

The sensor is not suitable for determinations of concentrations via measurement of color intensity (colorimetry).

Phụ kiện tùy chọn

Order no.	Description
-----------	-------------

6.02109.000 OMNIS adapter cable

This adapter cable comprising socket F to plug P is suitable for use as a fixed cable (e.g. Optrode or Solvotrode easyClean) connecting a sensor without temperature sensor to the OMNIS analog measuring module.



6.02117.000 USB power supply unit 5 V / 2.1 A

USB charging device for 946 Portable VA Analyzer.

Power supply unit for the power supply of the 6.1115.100 Optrode if there is no USB connector available for this purpose on a Metrohm device (e.g. with older devices).

