



Thin-Layer cell

6.1257.100

Amperometric detector cell with Thin-Layer geometry. For special applications and systems with higher backpressure (e.g. amperometry MS couplings).

Phụ kiện tùy chọn

Order no.	Description
6.1257.820	50 µm spacer to Thin-Layer cell
	50 µm spacer for the amperometric Thin-Layer cell, 3 pcs.



6.1257.840

25 µm spacer to Thin-Layer cell

25 µm spacer for the amperometric Thin-Layer cell, 3 pcs.



6.5000.200

Accessory kit: IC Amperometric Detector

Optional accessory kit for the IC Amperometric Detector for determinations in low-conductivity solutions.

