



Connecting cable, leak sensor

6.2141.430

Connecting cable between connection box and leak sensor inlet of the IC

Phụ kiện tùy chọn

Order no.	Description
6.2141.410	Remote cable, IC - Agilent ICP-MS
	Connecting cable for synchronization of Metrohm IC Systems (930 IC Flex and 940 Professional IC) and Agilent ICP-MS systems



6.2149.310 Connection Box, remote control, ICP-MS

Connector for use as interface between Metrohm IC (Remote Box MSB) and Agilent ICP-MS in MassHunter 5.3 and higher.



6.2141.420 Connecting cable, Remote Box MSB

Connecting cable between connection box and Remote Box MSB

