



Macro pump head PEEK

6.2824.130

Macro pump head for intelligente IC instruments, flow range 0.1...20 mL/min, maximum pressure 12.5 MPa.

Phạm vi giao hàng 6.2824.130

Qt.	Order no.	Description
2 PCS	6.2741.040	PE/PTFE piston seal, macro
		For all macro pump heads



1 PCS

6.2824.170

Inlet valve PEEK

Metal-free check valve for the inlet side of the IC pump heads of the devices 940, 930, 925, 883, 882, 881, and 850.



1 PCS

6.2824.160

Outlet valve PEEK

Metal-free check valve for the outlet side of the IC pump heads of the devices 940, 930, 925, 883, 882, 881, and 850.

