



Aspiration tubing with coupling, for IC

6.5332.010

Phạm vi giao hàng 6.5332.010

Qt.	Order no.	Description
1 PCS	6.1834.080	Aspiration tubing, 2 m

Eluent aspiration tubing for Professional IC devices for connection to the IC degasser.

Optional:

6.2744.210 tubing adapter for aspiration filter

6.2821.090 aspiration filter

6.2744.230 adapter 1/16 in/2.5 mm for connecting the aspiration tubing to the IC pump if no degasser is present



1 PCS

6.2621.050

1/4 in. wrench

For 1/4 in. screws. For IC instruments



1 PCS

6.2739.000

Wrench

For tightening connectors




1 PCS

6.2744.210

Tubing adapter for aspiration filter (ProfilC)

For Professional IC instruments



1 PCS

6.2744.230

1/16 in. / 2.5 mm adapter

Adapter for the connection of the aspiration tubing to the IC pump.
Contains the pressure screw for the PEEK capillary.

