



IC equipment Wall-Jet cell: Anion (GC, Ag/AgCl).

6.5337.030

Equipment comprised of Wall-Jet cell with additional accessories. For anion analysis with a Glassy Carbon and an Ag/AgCl reference electrode.

Phạm vi giao hàng 6.5337.030

Qt.	Order no.	Description
1 PCS	6.1257.220	GC working electrode
Working electrode made of Glassy Carbon for amperometric detection, 3 mm diameter.		



1 PCS

6.1257.720

Ag/AgCl reference electrode for 6.1257.xxx

Silver/silver chloride reference electrode for amperometric detection.



1 PCS

6.1257.810

50 μ m spacer for the Wall-Jet cell.

50 μ m spacer for the amperometric Wall-Jet cell, 3 pcs.



1 PCS

6.1257.830

25 μ m spacer for the Wall-Jet cell

25 μ m spacer for the amperometric Wall-Jet cell, 3 pcs.



1 PCS

6.1831.010

PEEK capillary 0.25 mm i.d. / 3 m

For all IC components.



1 PCS

6.2621.140

Hexagon key 2.5 mm



1 PCS

6.2744.014

Pressure screw 2x

With UNF 10/32 connection. For the connection of PEEK capillaries



1 PCS

6.2802.000

Polishing set for solid-state electrodes

Polishing set with 1 polishing cloth and about 2 g aluminum oxide powder (grain size 0.3 µm)

