



772 Pump Unit

2.772.0110

可直接连接在样品处理器上的蠕动泵。

Scope of delivery 2.772.0110

Qt.	Order no.	Description
1 PCS	1.772.0110	772 Pump Unit 可直接连接在样品处理器上的蠕动泵。



2 PCS

6.1801.120

PVC 管 / 4 毫米 / 6 毫米 / 2 米



1 PCS

6.1812.000

PTFE (聚四氟乙烯) 管 4 mm / 6 mm / 4 m

用于冲洗，用在样品转换器和772型泵单元上



2 PCS

6.1820.050

适配器，M6 / 管接头

用于蠕动泵的泵管 6.1826.100。



1 PCS

6.1826.100

泵管 6.4 mm / 1 m

作为 772 Pump Unit 泵单元和 843 Pump Station (蠕动泵) 中所用泵管的替代品。



1 PCS

6.1828.000

PVDF 螺纹接套

用于容器 6.1621.000。



Optional accessories

Order no.	Description	
6.1826.160	氟橡胶泵管 用于蠕动泵。	
6.2160.010	适配器电缆 / 2 m / M8 插座 / 2 x 插头 B 适配器电缆 / 2 m / M8 插座 / 2 x 插头 B。用于 772 Pump Unit。	